


Warranty Card

user name	
e-mail	
mail address	
postal code	
contact number	
product name	
product model	
product barcode number	Batch number
name	
address	
contact number	
postal code	
sales date	
invoice barcode	



Monitor Quick Operation Manual


Button map



Operating instructions

1. Power on: press the power button to turn on, long press to turn off.
2. Channel selection: press the INPUT button, select the signal channel and then press the V-/V+ button to confirm.
3. Image effect design: Press the MENU button to enter the menu, press the P-/P+ button to select different items, respectively press the V+ button, press the V- button, adjust the value, and finally press the MENU button to exit.
4. Multimedia: Insert the U disk, press the INPUT button to select multimedia, press the V-/V+ button to confirm to enter the multimedia interface, press the V-/V+ button to select left and right, press the P-/P+ button to select different items, and then press the INPUT button to confirm.

Interface Diagram



Mark "only for safe use in non tropical climate"

HD Monitor

- HD: 1920*1080
- Rich colors: Nanotechnology is used to activate inert molecules twice to make the picture more layered.
- Bright colors: improved image quality, strong three-dimensionality.
- Clarity: detailed and realistic, conveying true colors.
- Built specifically for HD resolution products, this unit is optimized for HDMI input ports to reduce signal transmission loss and improve clarity.
- Support 4K 3860*2160, 2K 2560*1440 .



Mark "only for safe use in areas below 2000m above sea level"